


Toolholder form C1 axial, right hand, Shank Ø d1: 16mm

Order data

Order number	319100 16
GTIN	4045197373717
Item class	32V

Description
Version:

- Case-hardened HRC 58 ±2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

For plane cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, sheet 2.

Technical description

Shank Ø D ₁	16 mm
h ₆	22 mm
Shank width b ₃	13 mm
Colour code for VDI shanks	VDI 16
h ₁	12 mm
h ₂	17 mm
b ₂	24 mm

Data sheet

b_1	43 mm
h_5	20 mm
l_1	44 mm
Shape	C
Type of product	VDI tool arbor