

**Toolholder form B4 radial left-hand, short, Shank Ø d1: 50mm****Order data**

Order number	319060 50
GTIN	4045197373700
Item class	32V

Description**Version:**

- Case-hardened HRC 58 ±2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, sheet 2.

Technical description

h_5	35 mm
h_6	60 mm
h_2	41 mm
l_1	30 mm
Shank Ø D_1	50 mm

Data sheet

b_1	100 mm
l_2	55 mm
b_2	50 mm
h_1	32 mm
Colour code for VDI shanks	VDI 50
Shape	B
Type of product	VDI tool arbor