

SWISS TOOLS

## Toolholder axial single, left-hand, PSC 40, for toolholder square: 20 mm



### Order data

Order number	318902 20
GTIN	2050001715661
Item class	36D

### Description

#### Version:

With adjustable cooling nozzle with internal thread.

#### Application:

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

#### Note:

PSC clamping stud on request.

Through-coolant: yes

Overhang dimension A: 80 mm

Clamping length L<sub>1</sub>: 60 mm

B: 30 mm

External Ø D: 80 mm

### Technical description

Clamping length L <sub>1</sub>	60 mm
B	30 mm
Overhang dimension A	80 mm
for toolholder square	20 mm
External Ø D	80 mm
Adapter	PSC 40

Arbor standard	ISO 26623-2
Through-coolant	yes
Type of product	Steel toolholder