

SWISS TOOLS

Toolholder axial, triple, right-hand, PSC 50, for toolholder square: 20 mm



Order data

| | |
|--------------|---------------|
| Order number | 318925 20 |
| GTIN | 2050001714220 |
| Item class | 36D |

Description

Version:

With adjustable cooling nozzle with internal thread.

Application:

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

Note:

PSC clamping stud on request.

Through-coolant: yes

Overhang dimension A: 123 mm

Clamping length L_1 : 97 mm

B: 30 mm

External \varnothing D: 90 mm

Technical description

| | |
|--------------------------|--------|
| B | 30 mm |
| Clamping length L_1 | 97 mm |
| Overhang dimension A | 123 mm |
| for toolholder square | 20 mm |
| External \varnothing D | 90 mm |
| Adapter | PSC 50 |

| | |
|-----------------|------------------|
| Arbor standard | ISO 26623-2 |
| Through-coolant | yes |
| Type of product | Steel toolholder |