



## Quick-change tapping chuck, MT3, Tapping range: M3-12



### Order data

Order number	334645 M3-12
GTIN	4045197606808
Item class	32P

### Description

#### Version:

- **Compact design, with flexible length compensation by compression and tension.**
- **Adjustable lead-in pressures for different materials and taps.**

Morse taper DIN 228 B.

#### Application:

- **To produce threads that are true to gauge.**
- **For right-hand and left-hand thread.**
- **For NC machines and machining centres.**

#### Optional extras:

For quick-change tapping collets see No. 335420 – 335660.

#### Note:

- **Quick-change tapping heads in other shank types size M14 – M33 available on request.**
- **Quick-change tapping heads not suitable for internal coolant supply.**

Length compensation by compression: 7.5 mm

Length compensation by tension: 7.5 mm

External Ø D: 38 mm

Internal Ø D<sub>i</sub>: 19 mm

Overhang dimension A: 46 mm

### Technical description

External Ø D	38 mm
Length compensation by tension	7.5 mm
Overhang dimension A	46 mm

Tapping range	M3 – M12
Internal Ø D <sub>1</sub>	19 mm
Length compensation by compression	7.5 mm
Adapter	MT3
Type of product	Tapping head

## Accessories

Quick-change insert with safety slip clutch Tap shank Ø 9 mm	335610 9
Base extension with safety slip clutch Tap shank Ø 4,5 mm	335645 4,5
Quick-change collet without safety slip clutch Tap shank Ø 11 mm	335420 11
Quick-change insert with safety slip clutch Tap shank Ø 3,5 mm	335610 3,5
Quick-change collet without safety slip clutch Tap shank Ø 10 mm	335420 10
Quick-change collet without safety slip clutch Tap shank Ø 7 mm	335420 7
Quick-change insert with safety slip clutch Tap shank Ø 10 mm	335610 10
Quick-change insert with safety slip clutch Tap shank Ø 11 mm	335610 11
Base extension with safety slip clutch Tap shank Ø 3,5 mm	335645 3,5
Quick-change insert with safety slip clutch Tap shank Ø 4,5 mm	335610 4,5
Base extension with safety slip clutch Tap shank Ø 9 mm	335645 9
Quick-change insert with safety slip clutch Tap shank Ø 7 mm	335610 7
Base extension with safety slip clutch Tap shank Ø 8 mm	335645 8
Quick-change collet without safety slip clutch Tap shank Ø 6 mm	335420 6

Base extension with safety slip clutch Tap shank Ø 10 mm	335645 10
Quick-change collet without safety slip clutch Tap shank Ø 8 mm	335420 8
Quick-change insert with safety slip clutch Tap shank Ø 8 mm	335610 8
Quick-change collet without safety slip clutch Tap shank Ø 3,5 mm	335420 3,5
Quick-change collet without safety slip clutch Tap shank Ø 4,5 mm	335420 4,5
Quick-change collet set without safety slip clutch, 8 pieces	335460
Quick-change collet without safety slip clutch Tap shank Ø 9 mm	335420 9
Base extension with safety slip clutch Tap shank Ø 7 mm	335645 7
Quick-change insert with safety slip clutch Tap shank Ø 6 mm	335610 6
Base extension with safety slip clutch Tap shank Ø 6 mm	335645 6