

Garant

eco-toolholder form B4 radial left-hand, short, Shank \varnothing d1: 20 mm


Order data

Order number	319061 20
GTIN	4045197523679
Item class	31V

Description
Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

GARANT eco – For use with normal clamping toolholders, with GARANT eco – system grooving toolholders No. 273830 – 273891 and with GARANT eco – parting-off toolholders No. 273651.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: B

h_1 : 16 mm

h_2 : 22 mm

b_1 : 55 mm

b_2 : 30 mm

h_5 : 30 mm

h_6 : 25 mm

Technical description

l_2	30 mm
Shank $\varnothing D_1$	20 mm
l_1	16 mm
Colour code for VDI shanks	VDI 20
b_1	55 mm
h_1	16 mm
h_6	25 mm
h_2	22 mm
h_5	30 mm
b_2	30 mm
Shape	B
Type of product	VDI tool arbor