

## Garant

eco-toolholder, form B1 radial right-hand, short, Shank  $\varnothing$  d1: 50 mm



### Order data

Order number	319001 50
GTIN	4045197578747
Item class	31V

### Description

#### Version:

- Case-hardened HRC 58  $\pm$ 2.
- All functional faces ground.
- With ball type coolant nozzles.

**GARANT eco** For use with normal clamping toolholders, with GARANT eco – system grooving toolholders No. 273830 – 273891 and with GARANT eco – parting-off toolholders No. 273651.

#### Application:

Mainly for external machining.

#### Standard:

**ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.**

Shape: B

$h_1$ : 25 mm

$h_2$ : 34 mm

$b_1$ : 100 mm

$b_2$ : 50 mm

$h_5$ : 35 mm

$h_6$ : 60 mm

### Technical description

Shank $\varnothing D_1$	50 mm
Colour code for VDI shanks	VDI 50
$h_1$	25 mm
$h_2$	34 mm
$b_1$	100 mm
$l_2$	55 mm
$b_2$	50 mm
$h_6$	60 mm
$h_5$	35 mm
$l_1$	30 mm
Shape	B
Type of product	VDI tool arbor

---

## Accessories

Assembly wrench for ball nozzle Size 10	319003 10
---	-----------