

Garant**Eco toolholder, Form B3 radial right-hand, short, Shank Ø d1: 25mm**

Order data

Order number	319051 25
GTIN	4045197528384
Item class	31V

Description

Version:

- Case-hardened HRC 58 ±2.
- All functional faces ground.
- With ball type coolant nozzles.

GARANT Eco – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, sheet 2.

Technical description

b ₁	55 mm
l ₂	30 mm
h ₅	30 mm
h ₆	25 mm
h ₁	16 mm

Data sheet

h_2	22 mm
Colour code for VDI shanks	VDI 25
b_2	30 mm
l_1	16 mm
Shank $\varnothing D_1$	25 mm
Shape	B
Type of product	VDI tool arbor