

ALZMETALL
we drive productivity

Bench drill ALZTRONIC, maximum drill Ø in steel: 16 mm



Order data

Order number	076560 16
GTIN	2050001755384
Item class	03P

Description

Version:

High-speed, durable and precise bench drill.

- **AC motor 230 V, 50 Hz.**
- **Digital speed display.**
- **Stepless speed adjustment.**
- **Reversible.**
- **Swivelling spindle guard with electrical interlock.**
- **Mushroom-head pushbutton (latching) for EMERGENCY STOP.**
- **24-month warranty, 10-year spare part availability guarantee.**
- **Without drill chuck.**

With rigid and height-adjustable and swivelling machine table.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

Plates for other bench drills available on request.

Manufacturer's designation: ALZTRONIC 16

Power consumption: 540 W

maximum speed: 100 - 2000 rpm

Toolholder: MT2

maximum machine tap Ø in steel: M12

Spindle stroke: 80 mm

Technical description

Column Ø	65 mm
Spindle stroke	80 mm
Feed	manual
Distance spindle-base plate minimum	437 mm
maximum machine tap Ø in steel	M12
Machine baseplate width of usable area	300 mm
Machine table width of usable area	240 mm
Machine table length of usable area	300 mm
Distance spindle-base plate maximum	437 mm
Power consumption	540 W
maximum drill Ø in steel	16 mm
Toolholder	MT2
Distance spindle-machine table maximum	357 mm
Distance spindle-machine table minimum	75 mm
Machine table height adjustment	hand crank
Machine baseplate height of usable area	240 mm
Weight	83 kg
maximum speed	100 - 2000 rpm
Manufacturer's designation	ALZTRONIC 16
Throat	190 mm
T-slot nominal size	12 mm
Number of T-slots	2
T-slot pitch	80 mm