


Toolholder, form B1 radial right-hand, short, Shank \varnothing d1: 16 mm

Order data

Order number	319000 16
GTIN	4045197373632
Item class	32V

Description
Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: B

h_1 : 12 mm

h_2 : 17 mm

b_1 : 42 mm

b_2 : 25 mm

h_5 : 20 mm

h_6 : 22 mm

Technical description

b_2	25 mm
h_6	22 mm

h_1	12 mm
Shank $\varnothing D_1$	16 mm
b_1	42 mm
l_1	13 mm
h_5	20 mm
h_2	17 mm
l_2	24 mm
Colour code for VDI shanks	VDI 16
Shape	B
Type of product	VDI tool arbor

Accessories

Assembly wrench for ball nozzle Size 10	319003 10
---	-----------