


Toolholder form B2 radial left-hand, short, Shank Ø d1: 16mm

Order data

Order number	319010 16
GTIN	4045197373656
Item class	32V

Description
Version:

- Case-hardened HRC 58 ±2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, sheet 2.

Technical description

Colour code for VDI shanks	VDI 16
b ₁	42 mm
l ₂	24 mm
h ₅	20 mm
h ₂	17 mm
Shank Ø D ₁	16 mm

Data sheet

h_6	22 mm
h_1	12 mm
l_1	13 mm
b_2	25 mm
Shape	B
Type of product	VDI tool arbor