



Toolholder form B3 radial right-hand, short, Shank \varnothing d1: 16mm



Order data

Order number	319050 16
GTIN	
Item class	32V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

l_1	13 mm
h_6	22 mm
h_5	20 mm
Colour code for VDI shanks	VDI 16
l_2	24 mm
Shank \varnothing D ₁	16 mm
h_2	17 mm

b_2	25 mm
b_1	42 mm
h_1	12 mm
Shape	B
Type of product	VDI tool arbor