

Garant**Eco toolholder, Form B3 radial right-hand, short, Shank Ø d1: 30mm**

Order data

Order number	319051 30
GTIN	4045197523655
Item class	31V

Description

Version:

- Case-hardened HRC 58 ±2.
- All functional faces ground.
- With ball type coolant nozzles.

GARANT Eco – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, sheet 2.

Technical description

l_1	22 mm
h_6	35 mm
h_1	20 mm
Shank Ø D_1	30 mm
b_2	35 mm

Data sheet

h_5	38 mm
b_1	70 mm
h_2	29 mm
l_2	40 mm
Colour code for VDI shanks	VDI 30
Shape	B
Type of product	VDI tool arbor