



Toolholder form B2 radial left-hand, short, Shank \varnothing d1: 20 mm



Order data

Order number	319010 20
GTIN	4045197223906
Item class	32V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: B

h_1 : 16 mm

h_2 : 22 mm

b_1 : 55 mm

b_2 : 30 mm

h_5 : 30 mm

h_6 : 25 mm

Technical description

b_2	30 mm
h_1	16 mm

b ₁	55 mm
Shank Ø D ₁	20 mm
Colour code for VDI shanks	VDI 20
l ₁	16 mm
l ₂	30 mm
h ₂	22 mm
h ₅	30 mm
h ₆	25 mm
Shape	B
Type of product	VDI tool arbor