


Toolholder, form B1 radial right-hand, short, Shank \varnothing d1: 50mm

Order data

Order number	319000 50
GTIN	
Item class	32V

Description
Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

Shank \varnothing D ₁	50 mm
h ₁	32 mm
l ₁	30 mm
Colour code for VDI shanks	VDI 50
b ₁	100 mm
l ₂	55 mm
h ₅	35 mm

b ₂	50 mm
h ₆	60 mm
h ₂	41 mm
Shape	B
Type of product	VDI tool arbor

Accessories

Assembly wrench for ball nozzle Size 10	319003 10
---	-----------