



Toolholder form B3 radial right-hand, short, Shank \varnothing d1: 50 mm



Order data

Order number	319050 50
GTIN	4045197373687
Item class	32V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: B

h_1 : 32 mm

h_2 : 41 mm

b_1 : 100 mm

b_2 : 50 mm

h_5 : 35 mm

h_6 : 60 mm

Technical description

h_2	41 mm
Colour code for VDI shanks	VDI 50

l_1	30 mm
h_5	35 mm
h_6	60 mm
l_2	55 mm
h_1	32 mm
Shank $\varnothing D_1$	50 mm
b_2	50 mm
b_1	100 mm
Shape	B
Type of product	VDI tool arbor

Accessories

Assembly wrench for ball nozzle Size 10

319003 10