

Garant**Eco toolholder, Form B3 radial right-hand, short, Shank Ø d1: 50mm****Order data**

Order number	319051 50
GTIN	4045197578761
Item class	31V

Description**Version:**

- Case-hardened HRC 58 ±2.
- All functional faces ground.
- With ball type coolant nozzles.

GARANT Eco – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, sheet 2.

Technical description

l_2	55 mm
b_1	100 mm
Colour code for VDI shanks	VDI 50
h_6	60 mm
b_2	50 mm

Data sheet

h_2	34 mm
Shank $\varnothing D_1$	50 mm
h_5	35 mm
l_1	30 mm
h_1	25 mm
Shape	B
Type of product	VDI tool arbor