

# AEG

## Hammer drill, Type: KH28SXE



### Order data

Order number	075620 KH28SXE
GTIN	4002395194377
Item class	07A

### Description

#### Version:

- **1010 W combi hammer with FIXTEC adapter, for lightning-fast changeover between SDS-plus chuck and quick-clamping drill chuck.**
- **Pneumatic hammer mechanism.**
- **Electronic controls with stepless pre-selection of speed and impact.**
- **Safety clutch.**
- **2-speed planetary gearbox.**
- **Zero rotation and 16 possible chisel positions for easy chisel work.**
- **Anti-vibration system AVS and soft-grip for maximum user comfort.**
- **Soft-Grip for very good user comfort.**

#### Supplied with:

FIXTEC adapter, quick-clamping chuck 1.5 - 13 mm, SDS-plus bit holder, additional handle, drilling depth stop, transport case.

#### Attention:

German version. Order free UK adapter plug No. 08 1172\_GB.

Packaging: Carrying case

Schaft: SDS Plus

Manufacturer's designation: KH28SXE

Power consumption: 1010 W

maximum speed 1st speed: 0 - 1500 rpm

maximum twist drill size Ø in steel: 13 mm  
maximum twist drill size Ø in wood: 30 mm  
maximum twist drill size Ø in concrete: 28 mm

## Technical description

Weight	2.8 kg
Power consumption	1010 W
maximum speed 1st speed	0 - 1500 rpm
maximum hammer rate	5000 rpm
maximum vibration to EN	15.4 m/s <sup>2</sup>
maximum twist drill size Ø in steel	13 mm
maximum twist drill size Ø in concrete	28 mm
Impact energy	2.8 J
Manufacturer's designation	KH28SXE
Quick-clamping chuck range	1.5 - 13 mm
maximum twist drill size Ø in wood	30 mm
Skaft	SDS Plus
Packaging	Carrying case