


**Toolholder form B4 radial left-hand, short, Shank  $\varnothing$  d1: 16 mm**

**Order data**

Order number	319060 16
GTIN	4045197373694
Item class	32V

**Description**
**Version:**

- Case-hardened HRC 58  $\pm$ 2.
- All functional faces ground.
- With ball type coolant nozzles.

**Application:**

Mainly for external machining.

**Standard:**

**ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.**

Shape: B

$h_1$ : 12 mm

$h_2$ : 17 mm

$b_1$ : 42 mm

$b_2$ : 25 mm

$h_5$ : 20 mm

$h_6$ : 22 mm

**Technical description**

$h_1$	12 mm
-------	-------

$b_2$	25 mm
$l_1$	13 mm
$b_1$	42 mm
Shank $\varnothing D_1$	16 mm
$h_2$	17 mm
$h_5$	20 mm
$l_2$	24 mm
$h_6$	22 mm
Colour code for VDI shanks	VDI 16
Shape	B
Type of product	VDI tool arbor