

# mato

## Lube-Shuttle® pneumatic grease gun, 400 g



### Order data

Order number	083587
GTIN	4016553037307
Item class	08H

### Description

#### Version:

One-handed pneumatic grease guns, outstandingly well balanced. **Single-shot system for optimum grease management (1 cm<sup>3</sup> / stroke)**, pressure ratio 1:60.

Refilling with Lube-Shuttle® cartridges (contents: 400 g).

**Suitable for greases up to NLGI class 3 and very low temperatures.**

#### Supplied with:

Rubberised armoured hose, 4-jaw hydraulic push-on connector.

### Technical description

Working pressure	400 bar
Test pressure	800 bar
Hose connection thread	R1/8 in
Operational range compressed air supply	3 - 8 bar
Power supply	Pneumatic
Product name attribute	400 g
Type of product	Grease gun

---

## Accessories

Nozzle with universal connector Connection thread 1/8	083583 1/8
Nozzle with conical connector Connection thread 1/8	083584 1/8
Armoured hose with 4-jaw hydraulic push-on connector Connection thread 1/8	083586 1/8
Armoured hose with push-on connector Connection thread 1/8	083588 1/8
4-jaw hydraulic push-on connector Connection thread 1/8	083589 1/8
4-jaw hydraulic push-on connectorsafeLOCK Connection thread 1/8	083596 1/8