

Garant

eco-toolholder form B5 radial right-hand, long, Shank \varnothing d1: 30 mm



Order data

Order number	319071 30
GTIN	4045197584311
Item class	31V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

GARANT eco For use with normal clamping toolholders, with GARANT eco – system grooving toolholders No. 273830 – 273891 and with GARANT eco – parting-off toolholders No. 273651.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: B

h_1 : 20 mm

h_2 : 29 mm

b_1 : 100 mm

b_2 : 65 mm

h_5 : 38 mm

h_6 : 28 mm

Technical description

h_6	28 mm
h_1	20 mm
l_1	22 mm
l_2	40 mm
h_5	38 mm
Shank $\varnothing D_1$	30 mm
h_2	29 mm
b_2	65 mm
b_1	100 mm
Colour code for VDI shanks	VDI 30
Shape	B
Type of product	VDI tool arbor