

**Quick-change collet without safety slip clutch, M6 – M20, Tap shank Ø: 8mm****Order data**

Order number	335430 8
GTIN	4045197152558
Item class	32H

Description**Version:**

Rigid quick-change tapping collets **without** safety clutch.

Application:

For use with disengaging tapping head.

Note:

Inserts with slip clutch are supplied with the torque setting for machining steel (R_m 600 – 800 N/mm²). The setting can be modified as required by adjusting the nut.

Technical description

Tap shank Ø	8 mm
Shank square	6.2 mm
Tapping range	M6 – M20
External Ø D	46 mm
Shank Ø d	31 mm
Connection length L	35 mm

Overhang length H	11 mm
Type of product	Quick-change collet