

**Quick-change collet without safety slip clutch, M3 – 12, Tap shank Ø: 9mm****Order data**

Order number	335420 9
GTIN	4045197152503
Item class	32H

**Description****Version:**

Rigid quick-change tapping collets **without** safety clutch.

**Application:**

For use with disengaging tapping head.

**Note:**

Inserts with slip clutch are supplied with the torque setting for machining steel ( $R_m$  600 – 800 N/mm<sup>2</sup>). The setting can be modified as required by adjusting the nut.

**Technical description**

Tap shank Ø	9 mm
Shank square	7 mm
Tapping range	M3 – 12
External Ø D	30 mm
Shank Ø d	19 mm
Connection length L	21.5 mm

Overhang length H	7 mm
Type of product	Quick-change collet