


Toolholder form C1 axial, right hand, Shank Ø d1: 30mm

Order data

Order number	319100 30
GTIN	4045197191052
Item class	32V

Description
Version:

- Case-hardened HRC 58 ±2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

For plane cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, sheet 2.

Technical description

b ₁	70 mm
Colour code for VDI shanks	VDI 30
b ₂	35 mm
Shank Ø D ₁	30 mm
l ₁	70 mm
h ₅	28 mm
Shank width b ₃	17 mm

Data sheet

h_1	20 mm
h_2	29 mm
h_6	38 mm
Shape	C
Type of product	VDI tool arbor