



DS double-ended grinding machine, 400 V, Type: DS04/150



Order data

Order number	077512 DS04/150
GTIN	2050001674166
Item class	03S

Description

Version:

The **extremely smooth-running** motor ensures a long working life, even when run **continuously. Supplied without grinding wheels.**

Exceptionally robust three-phase double-ended bench grinding machines, bench-top type. Sturdy workpiece supports, restart inhibit, and eye protection shields ensure user safety.

Note:

Suitable grinding wheels can be found from No. 596100.

Technical description

maximum speed	2900 min ⁻¹
Weight	14 kg
Manufacturer's designation	DS04/150
Power consumption	250 W
Abrasive disc width T	25 mm
Abrasive disc hole Ø H	51 mm
Abrasive disc Ø D	150 mm
Power supply	Mains operated
Type of product	Double grinding machine

Accessories

Bench grinding wheel D×T×H (mm) Type NK60	596220 NK60
Tool mounting plate right-hand Type AT1	077525 AT1
Eye protection shield for No. 077502 Type DS1	077509 DS1
Tool mounting plate left-hand Type AT1	077519 AT1
Bench grinding wheel D×T×H (mm) Type SC80	596220 SC80
Bench grinding wheel D×T×H (mm) Type EK60	596220 EK60
Bench grinding wheel D×T×H (mm) Type EK80	596220 EK80
Support stand suitable for machine DS04	077513 DS04