

Garant**Eco toolholder, Form C3 axial, right hand, Shank Ø d1: 20mm****Order data**

Order number	319161 20
GTIN	4045197523761
Item class	31V

Description**Version:**

- Case-hardened HRC 58 ±2.
- All functional faces ground.
- With ball type coolant nozzles.

GARANT Eco – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

Application:

For plane cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, sheet 2.

Technical description

b ₂	27 mm
l ₁	55 mm
Shank Ø D ₁	20 mm
h ₂	22 mm
h ₆	30 mm

Data sheet

h_5	25 mm
Shank width b_3	13 mm
b_1	52 mm
h_1	16 mm
Colour code for VDI shanks	VDI 20
Shape	C
Type of product	VDI tool arbor