

Garant

eco-toolholder form C1 axial, right hand, Shank \varnothing d1: 30 mm



Order data

Order number	319101 30
GTIN	4045197523716
Item class	31V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

GARANT eco For use with normal clamping toolholders, with GARANT eco – system grooving toolholders No. 273830 – 273891 and with GARANT eco – parting-off toolholders No. 273651.

Application:

For plane cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: C

h_1 : 20 mm

h_2 : 29 mm

b_1 : 70 mm

b_2 : 35 mm

Shank width b_3 : 17 mm

h_5 : 28 mm

Technical description

b ₁	70 mm
Shank Ø D ₁	30 mm
b ₂	35 mm
Colour code for VDI shanks	VDI 30
h ₁	20 mm
h ₂	29 mm
Shank width b ₃	17 mm
h ₅	28 mm
l ₁	70 mm
h ₆	38 mm
Shape	C
Type of product	VDI tool arbor