

Garant

eco-toolholder form C2 axial, left-hand, Shank \varnothing d1: 40 mm



Order data

Order number	319111 40
GTIN	4045197523754
Item class	31V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

GARANT eco For use with normal clamping toolholders, with GARANT eco – system grooving toolholders No. 273830 – 273891 and with GARANT eco – parting-off toolholders No. 273651.

Application:

For plane cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: C

h_1 : 25 mm

h_2 : 34 mm

b_1 : 85 mm

b_2 : 42.5 mm

Shank width b_3 : 20.5 mm

h_5 : 32.5 mm

Technical description

h_6	48 mm
h_1	25 mm
l_1	85 mm
b_1	85 mm
Colour code for VDI shanks	VDI 40
h_5	32.5 mm
Shank $\varnothing D_1$	40 mm
h_2	34 mm
Shank width b_3	20.5 mm
b_2	42.5 mm
Shape	C
Type of product	VDI tool arbor