



Toolholder form C3 axial, right hand, Shank \varnothing d1: 16 mm



Order data

Order number	319160 16
GTIN	4045197373755
Item class	32V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

For plane cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: C

h_1 : 12 mm

h_2 : 17 mm

b_1 : 43 mm

b_2 : 24 mm

Shank width b_3 : 13 mm

h_5 : 20 mm

Technical description

b_1	43 mm
h_2	17 mm
l_1	44 mm

Shank width b_3	13 mm
b_2	24 mm
h_5	20 mm
Shank $\varnothing D_1$	16 mm
Colour code for VDI shanks	VDI 16
h_6	22 mm
h_1	12 mm
Shape	C
Type of product	VDI tool arbor