

**Garant**
**Base extension with safety slip clutch, M6–20, Tap shank Ø: 12mm**

**Order data**

Order number	335647 12
GTIN	4045197554130
Item class	31M

**Description**
**Version:**

Rigid quick-change tapping collets **without** safety clutch.

**Application:**

For Garant intermediate sections No. 338140 – 8142.

**Note:**

Inserts with slip clutch are supplied with the torque setting for machining steel ( $R_m$  600 – 800 N/mm<sup>2</sup>). The setting can be modified as required by adjusting the nut.

**Technical description**

Tap shank Ø	12 mm
Shank square	9 mm
Tapping range	M6–20
External Ø D	50 mm
Shank Ø d	31 mm
Connection length L	35 mm
Overhang length H	96 mm
Ø e	34.5 mm
Type of product	Extension

