

Garant**Eco toolholder, Form C1 axial, right hand, Shank Ø d1: 50mm**

Order data

Order number	319101 50
GTIN	4045197578785
Item class	31V

Description

Version:

- Case-hardened HRC 58 ±2.
- All functional faces ground.
- With ball type coolant nozzles.

GARANT Eco – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

Application:

For plane cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, sheet 2.

Technical description

Colour code for VDI shanks	VDI 50
b ₁	100 mm
l ₁	100 mm
Shank Ø D ₁	50 mm
h ₆	60 mm

Data sheet

h_1	25 mm
b_2	50 mm
h_5	50 mm
h_2	34 mm
Shank width b_3	26 mm
Shape	C
Type of product	VDI tool arbor