


Toolholder form C4 axial, left-hand, Shank Ø d1: 16mm

Order data

Order number	319170 16
GTIN	4045197373809
Item class	32V

Description
Version:

- Case-hardened HRC 58 ±2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

For plane cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, sheet 2.

Technical description

h_2	17 mm
h_1	12 mm
Colour code for VDI shanks	VDI 16
b_1	43 mm
Shank Ø D_1	16 mm
h_6	22 mm
l_1	44 mm

Data sheet

h_5	20 mm
b_2	24 mm
Shank width b_3	13 mm
Shape	C
Type of product	VDI tool arbor