



## Multi-purpose soldering iron, Heating power: 30W



### Order data

Order number	082100 30
GTIN	4003008047004
Item class	04C

### Description

#### Version:

Tough industrial soldering irons with **Ersadur long-life soldering tips** (30 times the working life of conventional copper soldering tips). **Warm-up time 3 min.** (for size 300, approx. 5 min.). Power cable 1.5 m rubber cable (PVC for size 30). **With support stand** (not size 30). Proven Erska soldering iron with attachable support stand.

### Technical description

Weight without power lead	80 g
Heating power	30 W
Soldering tip width	3.1 mm
suitable for copper cross sections up to	2.5 mm <sup>2</sup>
Soldering tip temperature after 3 minutes	380 °C
Power supply	Mains operated
Type of product	Soldering iron

### Accessories

Desoldering pump PDD03 plastic, antistatic	082355
Lead-free soldering wire Sn96.5, Ag3.0, Cu0.5, roll of 250 g Soldering wire Ø 1 mm	082365 1

Lead-free soldering wire Sn96.5, Ag3.0, Cu0.5, roll of 250 g  
Soldering wire Ø 1,5 mm

082365 1,5

Soldering tip Manufacturer's designation 32KD

082400 32KD