



Toolholder form C3 axial, right hand, Shank \varnothing d1: 20 mm



Order data

Order number	319160 20
GTIN	4045197373762
Item class	32V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

For plane cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: C

h_1 : 16 mm

h_2 : 22 mm

b_1 : 52 mm

b_2 : 27 mm

Shank width b_3 : 13 mm

h_5 : 25 mm

Technical description

b_2	27 mm
Colour code for VDI shanks	VDI 20
Shank width b_3	13 mm

h_5	25 mm
h_2	22 mm
Shank $\varnothing D_1$	20 mm
l_1	55 mm
h_1	16 mm
b_1	52 mm
h_6	30 mm
Shape	C
Type of product	VDI tool arbor