


Toolholder form C2 axial, left-hand, Shank \varnothing d1: 16 mm

Order data

Order number	319110 16
GTIN	4045197373731
Item class	32V

Description
Version:

- **Case-hardened HRC 58 \pm 2.**
- **All functional faces ground.**
- **With ball type coolant nozzles.**

Application:

For plane cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: C

h_1 : 12 mm

h_2 : 17 mm

b_1 : 43 mm

b_2 : 24 mm

Shank width b_3 : 13 mm

h_5 : 20 mm

Technical description

b_2	24 mm
h_6	22 mm
h_5	20 mm

h_1	12 mm
b_1	43 mm
l_1	44 mm
Shank width b_3	13 mm
Shank $\varnothing D_1$	16 mm
Colour code for VDI shanks	VDI 16
h_2	17 mm
Shape	C
Type of product	VDI tool arbor

Accessories

Assembly wrench for ball nozzle Size 10	319003 10
---	-----------