



Toolholder form C3 axial, right hand, Shank \varnothing d1: 30 mm



Order data

Order number	319160 30
GTIN	4045197373779
Item class	32V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

For plane cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: C

h_1 : 20 mm

h_2 : 29 mm

b_1 : 70 mm

b_2 : 35 mm

Shank width b_3 : 17 mm

h_5 : 28 mm

Technical description

h_1	20 mm
Shank width b_3	17 mm
h_6	38 mm

Shank $\varnothing D_1$	30 mm
Colour code for VDI shanks	VDI 30
b_1	70 mm
b_2	35 mm
h_2	29 mm
h_5	28 mm
l_1	70 mm
Shape	C
Type of product	VDI tool arbor