



## Compact angle grinder, Type: 722174



### Order data

Order number	077111 722174
GTIN	4014586875125
Item class	03F

### Description

#### Version:

**FEIN – Compact angle grinder Ø 125 mm.**

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

#### Supplied with:

Handle, safety guard, clamping nut, wrench.

Manufacturer's designation: WSG 8-125

Power consumption: 800 W

maximum speed: 11,000 min<sup>-1</sup>

maximum disc Ø: 125 mm

maximum cutting depth: 33 mm

Weight: 2 kg

### Technical description

Special features	Short body
maximum cutting depth	33 mm
Weight	2 kg
Power consumption	800 W
maximum vibration to EN	5 m/s <sup>2</sup>
maximum speed	11,000 min <sup>-1</sup>
Restart block	yes
maximum disc Ø	125 mm
Dead man's circuit	no
Manufacturer's designation	WSG 8-125
Power supply	Mains operated
Type of product	Angle grinder