

Garant**Base extension with safety slip clutch, M6–20, Tap shank Ø: 16mm****Order data**

Order number	335647 16
GTIN	4045197554154
Item class	31M

Description**Version:**

Rigid quick-change tapping collets **without** safety clutch.

Application:

For Garant intermediate sections No. 338140 – 8142.

Note:

Inserts with slip clutch are supplied with the torque setting for machining steel (R_m 600 – 800 N/mm²). The setting can be modified as required by adjusting the nut.

Technical description

Tap shank Ø	16 mm
Shank square	12 mm
Tapping range	M6–20
External Ø D	50 mm
Shank Ø d	31 mm
Connection length L	35 mm
Overhang length H	96 mm
Ø e	34.5 mm
Type of product	Extension

