

Garant

Shrink-fit chuck, slim, long 4°30', HSK-A 63 A = 120, Clamping range Ø D1: 8mm


Order data

Order number	308328 8
GTIN	4045197291776
Item class	31A

Description
Version:

- External taper 4°30'.
- With RFID/Balluffchip bore.
- HSK mating faces machined.

Application:

- For working in places where access is difficult.
- For clamping tools with parallel shank to h6 tolerance.

Optional extras:

Coolant pipe No. 309880, Plug-in socket No. 309890, Shrink-fit extension No. 302410 size 12/3 and 12/4. Shrink-fitting units No. 354210 – 354450.

Technical description

Overhang dimension A	120 mm
Ø D ₂	15 mm
Clamping Ø D ₁	8 mm
External Ø D	30 mm
Adapter	HSK-A 63 A = 120
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1

Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Type of product	Shrink-fit chuck

Accessories

Subframe cupboard	354290
Cooling adapter short4.5° for clamping \varnothing 6-9 mm	354235 6-9
Screening plate for coilSU1 for clamping \varnothing 6-12 mm	354240 6-12
Shrink-fit unit Type SU1	354210 SU1
Cooling unit Type CU1	354215 CU1
Cooling adapter long4.5° for clamping \varnothing 6-9 mm	354236 6-9