


Toolholder form C2 axial, left-hand, Shank \varnothing d1: 20 mm

Order data

Order number	319110 20
GTIN	4045197223968
Item class	32V

Description
Version:

- **Case-hardened HRC 58 \pm 2.**
- **All functional faces ground.**
- **With ball type coolant nozzles.**

Application:

For plane cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: C

h_1 : 16 mm

h_2 : 22 mm

b_1 : 52 mm

b_2 : 27 mm

Shank width b_3 : 13 mm

h_5 : 25 mm

Technical description

b_1	52 mm
h_1	16 mm
h_2	22 mm

Colour code for VDI shanks	VDI 20
b_2	27 mm
h_5	25 mm
Shank width b_3	13 mm
l_1	55 mm
h_6	30 mm
Shank $\varnothing D_1$	20 mm
Shape	C
Type of product	VDI tool arbor

Accessories

Assembly wrench for ball nozzle Size 10	319003 10
---	-----------