


**Toolholder form C3 axial, right hand, Shank  $\varnothing$  d1: 40 mm**

**Order data**

Order number	319160 40
GTIN	4045197373786
Item class	32V

**Description**
**Version:**

- Case-hardened HRC 58  $\pm$ 2.
- All functional faces ground.
- With ball type coolant nozzles.

**Application:**

For plane cutting in.

**Standard:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: C

$h_1$ : 25 mm

$h_2$ : 34 mm

$b_1$ : 85 mm

$b_2$ : 42.5 mm

Shank width  $b_3$ : 20.5 mm

$h_5$ : 32.5 mm

**Technical description**

$h_5$	32.5 mm
Shank $\varnothing$ D <sub>1</sub>	40 mm
$h_6$	48 mm

$b_1$	85 mm
Shank width $b_3$	20.5 mm
$h_1$	25 mm
$h_2$	34 mm
$l_1$	85 mm
Colour code for VDI shanks	VDI 40
$b_2$	42.5 mm
Shape	C
Type of product	VDI tool arbor