

**Garant**
**Base extension with safety slip clutch, M3 – 12, Tap shank Ø: 7mm**

**Order data**

Order number	335645 7
GTIN	4045197554031
Item class	31M

**Description**
**Version:**

Rigid quick-change tapping collets **without** safety clutch.

**Application:**

For GARANT intermediate sections No. 338140 – 338142.

**Note:**

Inserts with slip clutch are supplied with the torque setting for machining steel ( $R_m$  600 – 800 N/mm<sup>2</sup>). The setting can be modified as required by adjusting the nut.

**Technical description**

Tap shank Ø	7 mm
Shank square	5.5 mm
Tapping range	M3 – 12
External Ø D	32 mm
Shank Ø d	19 mm
Connection length L	21.5 mm
Overhang length H	70 mm
Ø e	23 mm
Type of product	Extension

