



## Toolholder form C2 axial, left-hand, Shank $\varnothing$ d1: 30 mm



### Order data

Order number	319110 30
GTIN	4045197223975
Item class	32V

### Description

#### Version:

- Case-hardened HRC 58  $\pm$ 2.
- All functional faces ground.
- With ball type coolant nozzles.

#### Application:

For plane cutting in.

#### Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Shape: C

$h_1$ : 20 mm

$h_2$ : 29 mm

$b_1$ : 70 mm

$b_2$ : 35 mm

Shank width  $b_3$ : 17 mm

$h_5$ : 28 mm

### Technical description

Shank $\varnothing$ D <sub>1</sub>	30 mm
Colour code for VDI shanks	VDI 30
$l_1$	70 mm

b <sub>1</sub>	70 mm
h <sub>1</sub>	20 mm
h <sub>6</sub>	38 mm
h <sub>5</sub>	28 mm
b <sub>2</sub>	35 mm
h <sub>2</sub>	29 mm
Shank width b <sub>3</sub>	17 mm
Shape	C
Type of product	VDI tool arbor

---

## Accessories

Assembly wrench for ball nozzle Size 10	319003 10
---	-----------