

Garant
ER collet chuck, PSC 63 short, for ER collet size: 40

Order data

Order number	308515 40
GTIN	4045197471635
Item class	31C

Description
Version:

- **With Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**

Application:

For clamping tools with plain shank in ER collets to DIN 6499 Form A and B.

Supplied with:

Coated high-speed clamping nut.

Optional extras:

ER collets No. 308881 – 309434. ER chuck key No. 309680 or 613300.

Coolant tube and assembling key for coolant tubes No. 309885 and 309893.

Through-coolant: yes

Clamping range: 3 - 26 mm

Overhang dimension A: 65 mm

External Ø D: 63 mm

Spare GARANT high-speed clamping nut No. 309610: 40

Technical description

Spare GARANT high-speed clamping nut No. 309610	40
for ER collets	40

Clamping range	3 - 26 mm
Overhang dimension A	65 mm
External Ø D	63 mm
Adapter	PSC 63 short
Arbor standard	ISO 26623-2
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Through-coolant	yes
Type of product	Collet chuck

Accessories

ER chuck key for ER collet chuck 40	309680 40
-------------------------------------	-----------