

SWISS TOOLS

## Screw-on toolholder neutral, PSC, Shank Ø / insert size – A dimension: 63/11-100 mm

### Order data

Order number	320370 63/11-100
GTIN	2050001712431
Item class	36D

### Description

#### Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No. 320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

Arbor standard: ISO 26623-2

Through-coolant: true

Overhang dimension A: 100 mm

suitable indexable insert: DC..11T3..

Spare part: S05

### Technical description

Through-coolant	yes
Adapter	PSC
Application type	neutral
Arbor standard	ISO 26623-2
Setting angle $\kappa$	62.5 degrees
Shank type	
Application example	Face turning
Application example	External longitudinal turning
Application	Face turning
Application	External longitudinal turning
Type of product	

