

**Garant**
**Whistle-Notch arbor, PSC 63 short, Clamping range  $\varnothing$  D1: 16mm**

**Order data**

Order number	308510 16
GTIN	4045197486240
Item class	31C

**Description**
**Version:**

- **With RFID/Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**

**Application:**

For clamping tools with suitable clamping flat (2°) to DIN 1835 Form E and DIN 6535 Form HE (= Whistle Notch).

**Optional extras:**

Coolant pipe No. 309885, coolant pipe wrench No. 309893.

**Technical description**

Clamping $\varnothing$ D <sub>1</sub>	16 mm
Overhang dimension A	80 mm
External $\varnothing$ D	48 mm
Adapter	PSC 63 short
Arbor standard	ISO 26623-1
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 μm
Machining strategy	HPC
Machining strategy	HSC
Type of product	Side lock arbor

---

## Accessories

Extension PSC-63 / PSC-63 A dimension 60 mm	318896 60
Extension PSC-63 / PSC-63 A dimension 100 mm	318896 100