

Garant
Whistle-Notch arbor, PSC 63 short, Clamping range \varnothing D1: 20mm

Order data

Order number	308510 20
GTIN	4045197486264
Item class	31C

Description
Version:

- **With RFID/Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**

Application:

For clamping tools with suitable clamping flat (2°) to DIN 1835 Form E and DIN 6535 Form HE (= Whistle Notch).

Optional extras:

Coolant pipe No. 309885, coolant pipe wrench No. 309893.

Technical description

Overhang dimension A	85 mm
Clamping \varnothing D ₁	20 mm
External \varnothing D	52 mm
Adapter	PSC 63 short
Arbor standard	ISO 26623-1
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 μm
Machining strategy	HPC
Machining strategy	HSC
Type of product	Side lock arbor

Accessories

Extension PSC-63 / PSC-63 A dimension 100 mm	318896 100
Extension PSC-63 / PSC-63 A dimension 60 mm	318896 60