

Garant
ER collet chuck, PSC 63 A = 100, for ER collet size: 40

Order data

Order number	308522 40
GTIN	4045197471673
Item class	31C

Description
Version:

- **With Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**

Application:

For clamping tools with plain shank in ER collets to DIN 6499 Form A and B.

Supplied with:

Coated high-speed clamping nut.

Optional extras:

ER collets No. 308881 – 309434. ER chuck key No. 309680 or 613300.

Coolant tube and assembling key for coolant tubes No. 309885 and 309893.

Through-coolant: yes

Clamping range: 3 - 26 mm

External Ø D: 63 mm

Spare GARANT high-speed clamping nut No. 309610: 40

Technical description

Spare GARANT high-speed clamping nut No. 309610	40
for ER collets	40
Clamping range	3 - 26 mm
External Ø D	63 mm

Adapter	PSC 63 A = 100
Arbor standard	ISO 26623-2
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Through-coolant	yes
Type of product	Collet chuck

Accessories

ER collet Nominal clamping Ø d 26 mm	308990 26
ER collet Nominal clamping Ø d 9 mm	308990 9
ER collet Nominal clamping Ø d 24 mm	309040 24
ER collet Nominal clamping Ø d 23 mm	309040 23
ER colletwith seal Nominal clamping Ø d 25 mm	308992 25
ER collet Nominal clamping Ø d 24 mm	308990 24
ER collet Nominal clamping Ø d 12 mm	309040 12
ER colletwith seal Nominal clamping Ø d 10 mm	308992 10
HiRunER clamping wrench for torque wrench Type 40	309749 40
ER collet set 23 pieces 4–26 mm	309320
ER chuck key for ER collet chuck 40	309680 40
ER colletwith seal Nominal clamping Ø d 12 mm	308992 12
ER collet Nominal clamping Ø d 10 mm	309040 10
ER colletwith seal Nominal clamping Ø d 14 mm	308992 14
ER collet Nominal clamping Ø d 7 mm	308990 7
ER collet Nominal clamping Ø d 11 mm	309040 11
ER collet Nominal clamping Ø d 19 mm	309040 19
ER collet Nominal clamping Ø d 17 mm	308990 17
ER collet Nominal clamping Ø d 14 mm	309040 14

ER collet Nominal clamping Ø d 6 mm	308990 6
ER colletwith seal Nominal clamping Ø d 8 mm	308992 8
ER collet Nominal clamping Ø d 14 mm	308990 14
ER collet Nominal clamping Ø d 17 mm	309040 17
ER collet Nominal clamping Ø d 18 mm	309040 18
ER collet Nominal clamping Ø d 12 mm	308990 12
ER collet Nominal clamping Ø d 10 mm	308990 10
ER collet Nominal clamping Ø d 20 mm	308990 20
ER collet Nominal clamping Ø d 5 mm	308990 5
ER collet Nominal clamping Ø d 16 mm	309040 16
ER collet Nominal clamping Ø d 15 mm	308990 15
ER colletwith seal Nominal clamping Ø d 16 mm	308992 16
ER collet Nominal clamping Ø d 9 mm	309040 9
ER colletwith seal Nominal clamping Ø d 22 mm	308992 22
ER collet Nominal clamping Ø d 25 mm	308990 25
ER collet Nominal clamping Ø d 19 mm	308990 19
ER colletwith seal Nominal clamping Ø d 6 mm	308992 6
ER collet Nominal clamping Ø d 23 mm	308990 23
ER colletwith seal Nominal clamping Ø d 18 mm	308992 18
ER colletwith seal Nominal clamping Ø d 20 mm	308992 20
ER collet Nominal clamping Ø d 11 mm	308990 11
ER collet Nominal clamping Ø d 25 mm	309040 25
ER collet Nominal clamping Ø d 4 mm	309040 4
ER collet Nominal clamping Ø d 22 mm	309040 22
ER collet Nominal clamping Ø d 7 mm	309040 7
ER collet Nominal clamping Ø d 15 mm	309040 15
ER collet Nominal clamping Ø d 4 mm	308990 4
ER collet Nominal clamping Ø d 21 mm	309040 21
ER collet Nominal clamping Ø d 21 mm	308990 21

ER collet Nominal clamping Ø d 22 mm	308990 22
ER collet Nominal clamping Ø d 20 mm	309040 20
ER collet Nominal clamping Ø d 26 mm	309040 26
ER collet Nominal clamping Ø d 8 mm	308990 8
ER collet Nominal clamping Ø d 18 mm	308990 18
ER collet Nominal clamping Ø d 5 mm	309040 5
ER collet Nominal clamping Ø d 6 mm	309040 6
ER collet Nominal clamping Ø d 8 mm	309040 8
ER collet Nominal clamping Ø d 16 mm	308990 16
ER collet set 23 pieces 4–26 mm	309028
ER collet Nominal clamping Ø d 13 mm	308990 13
ER collet Nominal clamping Ø d 13 mm	309040 13