



Soldering station, Manufacturer's designation: ICON1



Order data

Order number	082301 ICON1
GTIN	4003008085976
Item class	04K

Description

Version:

Temperature-controlled soldering station with ceramic PTC heating element and internally-heated Ersadur long-life soldering tips (precise temperature control). **Multi-functional anti-static high performance soldering station** with large display, memory for calibration data, standby sensor, 3 power level settings, and shut-off function. Using the i-Set tool option, station settings can easily be downloaded on to a USB stick and transferred to other stations.

Application:

For all professional electronics and electrical soldering applications.

Technical description

Manufacturer's designation	ICON1
Heating power	150 W
Weight of soldering iron without power cable	30 g
Control range of soldering tip temperature	150 - 450 °C
Warm-up time to 280 °C	approx. 9 s
Heating power	80 W
Power supply	Mains operated
electrostatic characteristic	EGB/ESD

Type of product	Soldering station
-----------------	-------------------

Accessories

Lead-free soldering wire Sn96.5, Ag3.0, Cu0.5, roll of 250 g Soldering wire Ø 1,5 mm	082365 1,5
Lead-free soldering wire Sn96.5, Ag3.0, Cu0.5, roll of 250 g Soldering wire Ø 1 mm	082365 1
Desoldering pump PDD03 plastic, antistatic	082355
Solder grease, 20g	082370
Soldering tip Manufacturer's designation PDLF10	082401 PDLF10
Soldering tip Manufacturer's designation CDLF12	082401 CDLF12
Soldering tip Manufacturer's designation CDLF32	082401 CDLF32