

SWISS TOOLS

Screw-on toolholder neutral, PSC, Shank Ø / insert size – A dimension: 63/16-130 mm

Order data

Order number	320380 63/16-130
GTIN	2050001712455
Item class	36D

Description

Note:

Appropriate spare parts No. 320610 – 320626 can be found in the spare parts list.

Arbor standard: ISO 26623-2

Through-coolant: true

Overhang dimension A: 130 mm

suitable indexable insert: VB..1604..

Spare part: S07

Technical description

Application type	neutral
Arbor standard	ISO 26623-2
Through-coolant	yes
Adapter	PSC
Setting angle κ	72.5 degrees
Shank type	
Application example	External longitudinal turning
Application	Face turning
Application	External longitudinal turning
Type of product	

